

DYMO[®]

practically genius

DYMO Industrial Labels

Label it fast, label it once, label it right.



Tough, jobsite-tested labels for industrial applications.

Rely on DYMO® Industrial Labels.

DYMO Industrial labels are tough – jobsite tested and UL recognized. Thermal transfer printing means labels won't smudge, smear or fade. Choose up to a one-inch label width in a broad assortment of materials and colors that meet OSHA, ANSI, and ISO standards. All DYMO Industrial labels are distributed from an easy-to-load cartridge, and with a split-back design, peeling and applying is quick and easy.

DYMO Industrial labels help you get labeling jobs done fast, and done right – the first time.



DYMO Industrial Labels are available in:

Flexible Nylon
Permanent Polyester
Indoor/Outdoor Vinyl
Heat-Shrink Tube
Non-Adhesive Tag
Self-Laminating




Labels



DYMO Industrial Label benefits:

- 1 Industrial-strength adhesives resist moisture, extreme temperatures, UV light and more – so labels won't curl or fall off
- 2 Available in a range of UL recognized materials for virtually every industrial labeling application; heat-shrink tubes tested to SAE, ASTM and military specifications
- 3 Thermal transfer printing technology – label text won't smudge, smear, or fade
- 4 Choose from 1/4", 3/8", 1/2", 3/4" and 1" label widths in a broad color assortment that meet OSHA, ANSI, and ISO standards
- 5 Easy-to-peel split back design makes applying labels quick and easy

The right label for virtually every situation and surface.



Indoor/Outdoor Vinyl

For general labeling or extreme conditions. Vinyl labels offer moisture, chemical and UV resistance, making them ideal for labeling both indoors and outdoors. Available in the widest range of colors that adhere to OSHA, ANSI and ISO color standards.

UL recognized as a component to UL 969

Flexible Nylon

For labeling wires, cables and rounded surfaces. Flexible Nylon labels conform and stick tightly to wires, cables, curved and textured surfaces. Tear-proof material resists damage when pulled through tight spaces or conduits.

UL recognized as a component to UL 969

Permanent Polyester

For labeling panels, blocks, faceplates, shelves, bins, beams and more. Permanent Polyester labels have a polished finish that leaves your work looking professional. Available in smaller widths that fit most patch panels, blocks and other distribution panels.

UL recognized as a component to UL 969

Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables. Print directly on Heat-Shrink Tubes with any DYMO Industrial labeling tool.

Meets MIL-M-81531, MIL-STD-202G, SAE-DTL- 23053/5 (Class 1 & 3)
UL recognized as a component to UL 224

Non-Adhesive Tag

For sliding into racks or faceplates that do not require adhesive. Made from polyester for increased durability.

Self-Laminating

Self-Laminating labels protect your printed area from exposure to oil, solvents, water and abrasion when applied to wires and cables.

All DYMO Industrial labels are RoHS compliant.


For technical specifications on all DYMO Industrial label types, please visit our website at: www.dymo.com/industrial

How to choose the right DYMO® Industrial label:

ENVIRONMENT	Heat/Cold Resistant	UV Light Resistant	Oil Resistant	Water Resistant	Chemical Resistant	Color Coding
SURFACE						
Cable/Wire	Flexible Nylon Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl
Curved Surface	Flexible Nylon Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl Flexible Nylon	Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl Flexible Nylon	Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl
Flat Surface	Permanent Polyester Flexible Nylon	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl
Textured Surface	Permanent Polyester Flexible Nylon	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl

Top = Best Option Bottom = Alternate Option

Available DYMO® Industrial label widths and colors:



IND	LABEL APPLICATIONS	LABEL COLOR	1/4"	3/8"	1/2"	3/4"	1"
			6mm	9mm	12mm	19mm	24mm
Labels that stick and stay stuck. DYMO Industrial labels are tough– jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labeling to OSHA, ISO and ANSI color standards or labeling in harsh conditions, DYMO Industrial labels have you covered. DYMO Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces. LEARN MORE: www.dymo.com/industrial		BLACK ON WHITE	-	18443	18444	18445	1805430
		BLACK ON YELLOW	-	-	18432	18433	1805431
		BLACK ON ORANGE	-	-	18435	18436	1805427
		BLACK ON GREY	-	-	1805413	1805419	1805425
		WHITE ON RED	-	-	1805416	1805422	1805429
		WHITE ON BLACK	-	1805437	1805435	1805436	1805432
		WHITE ON GREEN	-	-	1805414	1805420	1805426
		WHITE ON BLUE	-	-	1805243	1805417	1805423
VINYL Length 18' 5.5m - UL Recognized Component to UL969 - RoHS compliant 		WHITE ON PURPLE	-	-	1805415	1805421	1805428
		WHITE ON BROWN	-	-	1805412	1805418	1805424
		BLACK ON WHITE	1805442	18482	18483	18484	1734523
PERMANENT POLYESTER Length 18' 5.5m - UL Recognized Component to UL969 - RoHS compliant 		BLACK ON CLEAR	1805440	18508DMO	622289	622290	1805433
		BLACK ON METALLIC	1805441	18485	18486	18487	1805434
		BLACK ON WHITE	18051	18053	18055	18057	-
HEAT-SHRINK TUBE Length 5' 1.5m - UL Recognized Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant 		BLACK ON YELLOW	18052	18054	18056	18058	-
		BLACK ON WHITE	-	-	18488	18489	1734524
FLEXIBLE NYLON Length 11.5' 3.5m - UL Recognized Component to UL969 - RoHS compliant 		BLACK ON YELLOW	-	-	18490	18491	1734525
		BLACK ON WHITE	18111	-	18113	-	-
NON-ADHESIVE TAG Length 18' 5.5m - RoHS compliant 		BLACK ON WHITE	18111	-	18113	-	-
SELF-LAMINATING Length 18' 5.5m - RoHS compliant 		BLACK ON WHITE	-	-	-	-	1734821

DYMO, the DYMO logo and Rhino are trademarks or registered trademarks of Sanford, L.P. or its affiliates. All other trademarks are the property of their respective owners.

Distributed by:
 DYMO, Atlanta, GA 30328
 800-426-7827 www.dymo.com
 © 2011 Sanford, L.P.

11-0208

